

INFORMATION SHEET

Disinfecting tunnel Clean Tunnel FS



INTENDED USE:

CLEAN TUNEL^{FS} is designed to disinfect shopping trolleys. It ensures high disinfection efficiency thanks to a two-stage disinfection system with UV-C lamps and an agent destroying bacteria, fungi and viruses. Stainless steel construction, proven components and modern solutions guarantees long and trouble-free operation of the device. The control system allows you to program the decontamination time and the amount of disinfectant solution used.

HOW TO USE:

After placing the shopping trolley in the tunnel, activate the start button, the UV-C lamps are on and they radiate the trolley removing bacteria, fungi and viruses from its surface. The nozzle system then distributes the disinfectant solution over the entire surface of the trolley, decontaminating it and removing the remaining contamination. After disinfection, the disinfected trolley is released from the tunnel exit.

Technical parameters

Disinfecting tunnel CLEAN TUNEL FS

CLEAN TUNEL FS



Application	Contactless disinfection of shopping trolleys
External dimensions	1200 x 1250 x 1250 mm (W x D x H)
Passage dimensions	1000 x 1200 x 1100 mm (W x D x H)
Housing material	Stainless steel
Operating temperature	-10 deg. +50 deg. Celsius
Weight	100 kg
Power supply	230V/50Hz
Disinfection method	1. Radiation with UV-C lamps 2. Misting with disinfectant
UV-C lamps	Lamps emitting ultraviolet radiation UV-C
Disinfecting agent	Disinfectant is used for to remove viruses, bacteria and fungi, it is sprayable. Complete approvals and certifications.
Capacity	ca. 2000 trolleys/23 litres
Container volume:	23 litres
Container and pump	Acidproof steel
Number of spray nozzles	12
Operating mode	Automatic
Country of origin	Poland
Warranty	12 months